

# Maxilift-Set

## Dent repair system with Maxilift lever

Art. No. 0691 500 139

**Maxilift allows the gentle and perfect repair of deformations. Alternative equipment to dent lifter.**

**Bonding instead of welding. The following advantages of the bonding technique permit efficient work:**

- Otherwise required preliminary work is not necessary  
→ no disconnection of the battery, no connection of welding mass.
- Low heat generation during bonding omits extensive finishing work on ever more complicated vehicles  
→ no sealing of inside of sheet metal, no disassembly of interior panels, airbags, electrical components, etc.
- The bonding technique allows universal applications  
→ straightening of various different materials (steel, aluminium, stainless steel) and critical work, e.g. motorcycle tanks.
- No damage to undamaged paintwork  
→ cost-effective dent repair without repainting.
- One-hand operation of Maxilift permits supporting hammer work on the boundary area of the dent  
→ the straightened dent is stabilized and stress-free.
- The Maxilift system can be expanded with further dent repair tools  
→ extension for triple claw, Art. No. 0691 500 143 and electrode coupling, Art. No. 0691 500 142.



Item	Designation	Set-Cont.	Art. No.	
1	Maxilift	1	0691 500 140	1
2	Dent puller, drawing piece	1	0691 500 141	1
3	Glue stick (special glue, Ø 12 mm)	5	0890 100 057	26
4	Adapter, round, rigid (yellow) Ø 40 mm	3	0691 500 115	10
5	Adapter, oval, rigid (yellow) 47 x 33 mm	3	0691 500 117	10
6	Adapter, round, flexible (violet) Ø 40 mm	3	0691 500 116	10
7	Adapter, oval, flexible (violet) 47 x 33 mm	3	0691 500 118	10
8	Adapter, drum shaped, (violet) 47 x 33 mm	-	0691 500 122	10
9	Adapter, round, small (blue) Ø 35 mm	3	0691 500 121	10
10	Placer for adapter (for optimal placing and removal)	1	0691 500 114	1
11	Special spatula, flexible (easy removal of glue)	1	0691 500 120	1
12	Gloves, size 9 (protection against burns)	1	0899 410 09	1
13	Sanding fabric (roughens adapters prior to first use)	2	0585 44 600	10
14	Cleaning cloth (optimal for acetone and pre-cleaners)	50	0899 800 901	500
15	Acetone cleaner (residue-free cleaning of dents)	1	0893 460	1
16	Pre-cleaner (gentle removal of hot-melt glue)	1	0893 200 1	1

